

Elmasonic P 70 H

EMA

Ultrasonic cleaning unit

Elma Order Nos.	
Elmasonic P 70 H (220-240 V)	101 3735
Elmasonic P 70 H (115-120 V)	103 3325
Basket stainless steel	100 4247
Cover (plastic)	100 3283
Further accessories on request	



The Elmasonic P is the ideal unit for professional applications in analytical and medical laboratories and in industrial production processes. The unit series consists of 6 different unit sizes with tank capacities ranging from 2.75 to 28 litre. Microprocessor-controlled ultrasonic cleaning with multi-frequency technology (37/80 kHz) and special features are perfect for intensive cleaning tasks and laboratory applications. As the units are more powerful than standard ultrasonic cleaning units, and the ultrasonic power can be reduced electronically depending on the cleaning task.

Further advantages

- ultrasonic tank made of cavitation-proof stainless steel
- casing made of stainless steel, hygienic and easy to clean
- sandwich-type performance transducer systems
- two ultrasonic frequencies, switchable in one unit: 37 kHz und 80 kHz 37 kHz: for the removal of coarse contaminations and for mixing, dissolving, dispersing and degassing 80 kHz: perfect for the cleaning of capillaries and fort he use in quiet work areas, prolonged cleaning period
- automatic frequency switch-over for simultaneous coarse and fine cleaning
- activatable Sweep mode for an optimised sound field distribution within the cleaning bath
- activatable Pulse mode for an intensified ultrasonic cleaning power, additional ultrasonic power up to 20%
- activatable Degas mode for the quick degassing of HPLC samples or solvents and of fresh cleaning liquids
- Auto Degas mode for an automatic degassing cycle, e.g. for fresh cleaning liquids
- ultrasonic power variable for sensitive surfaces
- temperature-controlled ultrasonic operation: ultrasound starts automatically as soon as the preset temperature is reached
- indication of unit settings (e.g. set and actual values) by alphanumerical display
- saving of the last unit settings at switch-off
- electronic turning knobs
- drain duct mounted to the unit rear, operation of the drain duct on the unit side
- automatic stirring during heating-up process
- pluggable mains cable
- automatic safety switch-off after 12 h operation to prevent unintended permanent operation
- automatic safety switch-off at 90 °C to protect the cleaning items against excess temperatures

Technical data			
Mains voltage (Vac)	115-120 V/220-240 V	Weight (kg)	5.6
Ultrasonic frequency (kHz)	37 / 80	Material tank	stainless steel V2A
Power consumption total P 70 H (W)	970	Material casing	stainless steel V2A
Ultrasonic power effective (W)	220	Drain	3/8"
Ultrasonic peak performance max.(W)	880	CE-compliant	
Heating power (W)	750	Protection class	IP 20
Unit outer dimensions W/D/H (mm)	568 / 179 / 221	Sound pressure level (LpAU) * (dB)	<70
Tank internal dimensions W/D/H (mm)	505 / 137 / 100	Ultrasonic sound level (LpZ) ** (dB)	<105
Basket internal dimensions W/D/H (mm)	465 / 106 / 50		
Max. filling volume tank (lit.)	6.9	Ultrasonic sound level (LpZ) ** (dB) <105	

* Sound pressure level measured with basket and cover at a distance of 1 m

Subj

 ** Ultrasonic sound level measured with basket and cover at a distance of 1 m $\,$

Elma Schmidbauer GmbH · Gottlieb-Daimler-Str. 17 · D-78224 Singen · Fon +49 (0) 7731 882-0 · Fax +49 (0) 7731 882-266 · info@elma-ultrasonic.com www.elma-ultrasonic.com